

Ordering codes for Tmax XT accessories

Remote control



YO – shunt opening release

Shunt opening release – YO

Size	Type	Fixed/plug-in	Withdrawable
		U.S. Ordering Code	U.S. Ordering Code
Uncabled version			
XT5-XT6	YO 12 V DC	KXTFYOA	–
XT5-XT6	YO 24...60 V AC/DC	KXTFYOB	–
XT5-XT6	YO 110..240 V AC – 110..250 V DC	KXTFYOD	–
XT5-XT6	YO 380...525 V AC	KXTFYOG	–
Cabled version			
XT5	YO 12 V DC	KXTFYOCFPA	KXT5YOCWA
XT5	YO 24...60 V AC/DC	KXTFYOCFPB	KXT5YOCWB
XT5	YO 110..240 V AC – 110..250 V DC	KXTFYOCFPD	KXT5YOCWD
XT5	YO 380...525 V AC	KXTFYOCFPG	KXT5YOCWG
XT6	YO 12 V DC	KXTFYOCFPA	KXT6YOCWA
XT6	YO 24...60 V AC/DC	KXTFYOCFPB	KXT6YOCWB
XT6	YO 110..240 V AC – 110..250 V DC	KXTFYOCFPD	KXT6YOCWD
XT6	YO 380...525 V AC	KXTFYOCFPG	KXT6YOCWG



Shunt opening release – YO

Shunt opening release – YO

Size	Type	U.S. Ordering Code
XT7-XT7 M	YO 24 V AC/DC	ZEASA
XT7-XT7 M	YO 30 V AC/DC	ZEASB
XT7-XT7 M	YO 48 V AC/DC	ZEASC
XT7-XT7 M	YO 60 V AC/DC	ZEASD
XT7-XT7 M	YO 110-120 V AC/DC	ZEASE
XT7-XT7 M	YO 120-127 V AC/DC	ZEASF
XT7-XT7 M	YO 220-240 V AC/DC	ZEASG
XT7-XT7 M	YO 240-250 V AC/DC	ZEASH
XT7-XT7 M	YO 380-400 V AC	ZEASK
XT7-XT7 M	YO 415-440 V AC	ZEASL
XT7-XT7 M	YO 480-500 V AC	ZEASM